

**Garant**
**VB.T 160408, Grade: HB7130-2**


### Order data

Order number	261234 HB7130-2
GTIN	4062406750428
Item class	21G

### Description

VB.T 160408 HB7130-2 Grade: HB7130-2  
 Chip breaker: VM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 70 - 240 m/min

### Technical description

Tolerance	M
Cutting speed $v_c$ main application	70 - 240 m/min
Feed $f$	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Chip breaker	VM
ISO code indexable insert	VBMT 160408
Cutting conditions	slightly interrupted

Cutting depth $a_p$	0.5 - 2.5 mm
Number of changes/inserts	2
Main application	M
Tool material	Carbide
Grade	HB7130-2
Corner radius	0.8 mm
Type of product	Indexable insert for turning