



HOLEX CleverDrill HSS jobber drill, long N, uncoated, Ø DC h8: 5,1mm



Order data

Order number	116051 5,1
GTIN	4062406745257
Item class	12B

Description

Version:

HOLEX CleverDrill – Sturdy drill for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Successor product to No. 116050.

Technical description

recommended maximum drilling depth L_2	79.4 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.04 mm/rev.
Overall length L	132 mm
Flute length L_c	87 mm
Tolerance nominal \varnothing	h8
Point angle	118 degrees
Shank $\varnothing D_s$	5.1 mm
Number of cutting edges Z	2
Nominal $\varnothing D_c$	5.1 mm

Standard	DIN 340
Shank	Plain shank
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	64 m/min	N
Aluminium (short chipping)	suitable	52 m/min	N
Alu > 10% Si	suitable	40 m/min	N
Steel < 500 N/mm ²	suitable	26 m/min	P
Steel < 750 N/mm ²	suitable	26 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
GG(G)	suitable	24 m/min	K
CuZn	suitable	32 m/min	N
Oil	suitable		
wet maximum	suitable		