

Garant
Solid carbide milling cutter HPC, ZOx, Ø f8 DC: 16mm

Order data

Order number	202251 16
GTIN	4045197538611
Item class	11X

Description
Version:

Sturdy roughing end mill **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

Application:

For roughing milling with high demands on the component surface.

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 202017.

Technical description

No. of teeth Z	3
Overhang length L_1 incl. recess	100 mm
Feed f_z for side milling in short-chipping aluminium	0.12 mm
Shank form	HB
Feed f_z for slot milling in short-chipping aluminium	0.09 mm
Corner chamfer width at 45°	0.2 mm
Recess Ø D_1	15 mm
Cutting edge Ø D_c	16 mm
Shank Ø D_s	16 mm
Overall length L	150 mm
Flute length L_c	25 mm

Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal \varnothing	f8
Balance quality with shank	G 2.5 with HB
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	ZOX
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable	240 m/min	N
Alu > 10% Si	suitable	120 m/min	N
CuZn	suitable	120 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable only under restricted conditions
Air	suitable only under restricted conditions