


## Garant

### Solid carbide milling cutter with internal coolant supply HPC, ZOx, Ø f8 DC: 6mm



#### Order data

Order number	202255 6
GTIN	4045197413482
Item class	11X

#### Description

##### Version:

Sturdy roughing end mill **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

##### Application:

For roughing milling with high demands on the component surface.

##### Note:

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 202006.**

#### Technical description

Shank form	HA
Corner chamfer width at 45°	0.2 mm
No. of teeth Z	3
Overhang length L <sub>1</sub> incl. recess	18 mm
Cutting edge Ø D <sub>c</sub>	6 mm
Recess Ø D <sub>1</sub>	5.7 mm
Feed f <sub>z</sub> for side milling in short-chipping aluminium	0.08 mm
Feed f <sub>z</sub> for slot milling in short-chipping aluminium	0.06 mm
Shank Ø D <sub>s</sub>	6 mm
Overall length L	57 mm

Flute length $L_c$	13 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Tolerance nominal $\varnothing$	f8
Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	ZOX
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	yes
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable only under restricted conditions	500 m/min	N
Aluminium (short chipping)	suitable	480 m/min	N
Alu > 10% Si	suitable	240 m/min	N
CuZn	suitable	240 m/min	N
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable only under restricted conditions
<b>Services</b>	
Shank grinding Type HB	129100 HB