

**Garant****GARANT Master Alu Feed solid carbide drill, plain shank DIN 6535 HB, DLC, Ø DC h7: 8,01-Xmm****Order data**

Order number	122596 8,01-X
GTIN	4062406754341
Item class	11E

**Description****Version:**

**3-cutter tool**, specially developed for use at **very high feed rates** in aluminium. Outstandingly suitable for machines with **high power consumption** and stable machining conditions.

- **Specially developed cutter geometry, designed for very high feed rates, reduced cutting pressure and controlled chip breaking.**
- **Precision flute profile for reliable evacuation of chips.**
- **Achieve outstanding feed rates and tool life thanks to the third cutting edge.**

The sector-leading technology of the drill point for the tool guarantees optimum self-centring behaviour and permits spot drilling on irregular surfaces. 3 guidance lands guarantee a stable exit from the hole and an exact roundness of the hole.

**With DLC coating** – for longer tool lives, especially with aluminium with a higher Si content.

Coating on order – no return. Delivery time approx. 3 weeks if the basic item is available ex stock. Please note the minimum order quantity.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ . Delivery time: 10 weeks.

Minimum order quantity: 5 pieces.

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by +/-10% (minimum 1 piece).

**Technical description**

Shank Ø D <sub>s</sub>	10 mm
Number of cutting edges Z	3

## Data sheet

Overall length L	103 mm
Feed f in aluminium short-chipping	0.89 mm/rev.
Tolerance nominal Ø	h7
Flute length L <sub>c</sub>	61 mm
Standard	DIN 6537 L
Ø range	8.01 - 9 mm
Series	Master Alu
Coating	DLC
Tool material	solid carbide
Version	6×D
Type	W
Point angle	130 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	300 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	200 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		