

## Garant

### Solid carbide milling cutter MTC, uncoated, Ø DC: 20mm



#### Order data

Order number	202244 20
GTIN	4045197538536
Item class	11X

#### Description

##### Version:

**Eccentric relief ground**, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

**Without** 45° corner chamfer.

**Without** 45° corner chamfer.

Size 1–2 – tolerance: Size nominal Ø  $D_c = e8$ .

Size 2.5–20M – tolerance: Size nominal Ø  $D_c = h6$ .

##### Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

##### Note:

**NEW GENERATION AVAILABLE! Recommended successor product is No. 202002.**

#### Technical description

Cutting edge Ø $D_c$	20 mm
Feed $f_z$ for slot milling in short-chipping aluminium	0.085 mm
Overhang length $L_1$ incl. recess	52 mm
Shank form	HB
No. of teeth $Z$	3
Recess Ø $D_1$	19 mm
Feed $f_z$ for side milling in short-chipping aluminium	0.12 mm
Shank Ø $D_s$	20 mm
Overall length $L$	104 mm

Flute length $L_c$	41 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal $\varnothing$	h6
Balance quality with shank	G 2.5 with HB
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	W
Helix angle characteristic	unequal spacing
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	MTC
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable	190 m/min	N
Aluminium (short chipping)	suitable	150 m/min	N
Alu > 10% Si	suitable	120 m/min	N
PMMA acrylic	suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N
PEEK	suitable	130 m/min	N

PF 31	Suitable	110 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	180 m/min	N
Cu	Suitable	120 m/min	N
CuZn	Suitable	150 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		