

Garant**DNMG 150604, Grade: HU7305-1**

Order data

Order number	250760 HU7305-1
GTIN	4062406749811
Item class	21G

Description

DNMG 150604 HU7305-1 Grade: HU7305-1
Chip breaker: AM1
Tolerance: M
Cutting depth a_p : 0.2 - 5 mm
Feed f : 0.05 - 0.6 mm/rev.
Cutting speed v_c main application: 400 - 700 m/min

Technical description

Chip breaker	AM1
Corner radius	0.4 mm
Number of changes/inserts	4
Tolerance	M
Tool material	Carbide
Feed f	0.05 - 0.6 mm/rev.

Cutting speed v_c main application	400 - 700 m/min
Grade	HU7305-1
Coating	uncoated
Finishing/roughing assignment	Finishing
ISO code indexable insert	DNMG 150604
Main application	N
Cutting depth a_p	0.2 - 5 mm
Cutting conditions	slightly interrupted
Type of product	Indexable insert for turning