


Garant**WNMG 080408, Grade: HU7305-1**

Order data

Order number	252070 HU7305-1
GTIN	4062406749903
Item class	21G

Description

WN.G 080408 HU7305-1 Grade: HU7305-1
Chip breaker: AM1
Tolerance: M
Cutting depth a_p : 0.2 - 5 mm
Feed f : 0.05 - 0.6 mm/rev.
Cutting speed v_c main application: 400 - 700 m/min

Technical description

Main application	N
Tolerance	M
Chip breaker	AM1
Tool material	Carbide
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 5 mm
Corner radius	0.8 mm

Coating	uncoated
ISO code indexable insert	WNMG 080408
Cutting speed v_c main application	400 - 700 m/min
Cutting conditions	slightly interrupted
Number of changes/inserts	6
Feed f	0.05 - 0.6 mm/rev.
Grade	HU7305-1
Type of product	Indexable insert for turning