


Garant**WNMG 060408, Grade: HU7305-1**

Order data

Order number	252064 HU7305-1
GTIN	4062406749880
Item class	21G

Description

WN.G 060408 HU7305-1 Grade: HU7305-1
Chip breaker: AM1
Tolerance: M
Cutting depth a_p : 0.2 - 5 mm
Feed f : 0.05 - 0.6 mm/rev.
Cutting speed v_c main application: 400 - 700 m/min

Technical description

Main application	N
Corner radius	0.8 mm
Tolerance	M
Cutting depth a_p	0.2 - 5 mm
Cutting speed v_c main application	400 - 700 m/min
Cutting conditions	slightly interrupted
ISO code indexable insert	WNMG 060408

Tool material	Carbide
Number of changes/inserts	6
Chip breaker	AM1
Feed f	0.05 - 0.6 mm/rev.
Grade	HU7305-1
Finishing/roughing assignment	Finishing
Coating	uncoated
Type of product	Indexable insert for turning