


Garant
WNMG 080404, Grade: HU7305-1


Order data

Order number	252068 HU7305-1
GTIN	4062406749897
Item class	21G

Description

WN.G 080404 HU7305-1 Grade: HU7305-1

Chip breaker: AM1

Tolerance: M

Cutting depth a_p : 0.2 - 5 mm

Feed f : 0.05 - 0.6 mm/rev.

Cutting speed v_c main application: 400 - 700 m/min

Technical description

Feed f	0.05 - 0.6 mm/rev.
Tool material	Carbide
Cutting depth a_p	0.2 - 5 mm
Coating	uncoated
ISO code indexable insert	WNMG 080404
Cutting speed v_c main application	400 - 700 m/min
Corner radius	0.4 mm

Main application	N
Grade	HU7305-1
Tolerance	M
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Number of changes/inserts	6
Chip breaker	AM1
Type of product	Indexable insert for turning