

Garant
Toolholder with ratchet, All-steel, Overall length: 117mm

Order data

Order number	148701 117
GTIN	4062406754655
Item class	11K

Description
Version:

With two-jaw chuck for clamping square shanks. Moveable T-handle with a grooves centred and at each end for engaging the retaining ball. **Holder with stainless steel sheath.** Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness. **Heavy-duty version** for taps up to M20.

With head-side **hexagon** with 22 mm jaw width.

Application:

Suitable for tapping holes where access is difficult.

Note:

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

Technical description

Capacity <input type="checkbox"/>	8.5 - 12.5 mm
Overall length	110 mm
for hand taps DIN 352	M13 – M20
Spare jaws No. 148712 size	117
Material	All-steel
Type of product	Pin vice

