


Garant**SNMG 120408, Grade: HB7130-2**

Order data

Order number	251224 HB7130-2
GTIN	4062406749996
Item class	21G

Description

SNMG 120408 HB7130-2 Corner radius: 0.8 mm
Grade: HB7130-2
Chip breaker: VM
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Chip breaker	VM
Grade	HB7130-2
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	slightly interrupted
Number of changes/inserts	8
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	70 - 240 m/min

ISO code indexable insert	SNMG 120408
Main application	M
Corner radius	0.8 mm
Tool material	Carbide
Cutting depth a_p	0.5 - 4 mm
Type of product	Indexable insert for turning