


Garant
SNMG 120404, Grade: HB7130-2


Order data

Order number	251142 HB7130-2
GTIN	4062406749989
Item class	21G

Description

SNMG 120404 HB7130-2 Corner radius: 0.4 mm
 Grade: HB7130-2
 Chip breaker: VS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 270 m/min

Technical description

Cutting speed v_c main application	80 - 270 m/min
Main application	M
Corner radius	0.4 mm
Chip breaker	VS
Finishing/roughing assignment	Finishing
ISO code indexable insert	SNMG 120404
Tool material	Carbide

Number of changes/inserts	8
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	slightly interrupted
Grade	HB7130-2
Cutting depth a_p	0.3 - 2 mm
Type of product	Indexable insert for turning