

**Garant**
**TNMG 160408, Grade: HB7130-2**


### Order data

Order number	251544 HB7130-2
GTIN	4062406750015
Item class	21G

### Description

TNMG 160408 HB7130-2 Grade: HB7130-2

Chip breaker: VM

Tolerance: M

Cutting depth  $a_p$ : 0.5 - 5 mm

Feed  $f$ : 0.2 - 0.5 mm/rev.

Cutting speed  $v_c$  main application: 70 - 240 m/min

### Technical description

Feed $f$	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Chip breaker	VM
Corner radius	0.4 mm
Cutting depth $a_p$	0.5 - 5 mm
Tool material	Carbide
Tolerance	M

Grade	HB7130-2
ISO code indexable insert	TNMG 160404
Cutting conditions	slightly interrupted
Main application	M
Number of changes/inserts	6
Cutting speed $v_c$ main application	70 - 240 m/min
Type of product	Indexable insert for turning