

Garant**VNMG 160408, Grade: HB7130-2**

Order data

Order number	251804 HB7130-2
GTIN	4062406750039
Item class	21G

Description

VN.G 160408 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Grade	HB7130-2
ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Feed f	0.1 - 0.5 mm/rev.
Cutting conditions	slightly interrupted
Tool material	Carbide

Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	70 - 240 m/min
Tolerance	M
Corner radius	0.8 mm
Chip breaker	VM
Finishing/roughing assignment	Finishing
Main application	M
Type of product	Indexable insert for turning