

AEG

Cordless hammer drill / driver without battery or charger, Type: BSB18C2BL



Order data

Order number	070227 BSB18C2BL
GTIN	4058546324056
Item class	07A

Description

Version:

Powerful brushless 18 V cordless compact hammer drill/driver

- **Extremely handy due to a compact length of only 183 mm**
- **2-speed gearbox**
- **21-step torque and impact level setting for drilling in stone**
- **LED illumination of the working area**
- **Reversible**
- **PRO lithium-ion three-fold protection: Temperature monitoring, single-cell monitoring, overload protection**

Supplied with:

Cordless hammer drill/driver with belt clip, 1 pc. 13 mm FIXTEC quick-change chuck, **without battery, without charger.**

Technical description

Manufacturer's designation	BSB18C2BL-0
maximum twist drill size \varnothing in steel	13 mm

Weight without battery	1.6 kg
Battery voltage	18 V
maximum twist drill size Ø in concrete	13 mm
Power supply	Rechargeable battery-powered
Length	183 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
maximum speed 1st speed	500 min ⁻¹
maximum torque	60 Nm
maximum twist drill size Ø in wood	40 mm
maximum speed 2nd speed	1950 min ⁻¹
Motor design	Brushless
Type of product	limpact drill /screwdriver