

Garant**DNMG 110404, Grade: HB7130-2**

Order data

| | |
|--------------|-----------------|
| Order number | 250752 HB7130-2 |
| GTIN | 4062406750909 |
| Item class | 21G |

Description

DNMG 110404 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

| | |
|--------------------------------------|-------------------|
| Main application | M |
| Feed f | 0.2 - 0.5 mm/rev. |
| Cutting speed v_c main application | 70 - 240 m/min |
| Corner radius | 0.4 mm |
| Grade | HB7130-2 |
| ISO code indexable insert | DNMG 110404 |

| | |
|-------------------------------|------------------------------|
| Cutting depth a_p | 0.5 - 5 mm |
| Tool material | Carbide |
| Finishing/roughing assignment | Finishing |
| Tolerance | M |
| Number of changes/inserts | 4 |
| Cutting conditions | slightly interrupted |
| Chip breaker | VM |
| Type of product | Indexable insert for turning |