

Garant**DNMG 150608, Grade: HB7130-2**

Order data

Order number	250660 HB7130-2
GTIN	4062406750893
Item class	21G

Description

DNMG 150608 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	4
Main application	M
ISO code indexable insert	DNMG 150608
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	80 - 270 m/min
Tool material	Carbide

Grade	HB7130-2
Corner radius	0.8 mm
Chip breaker	VS
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning