

Garant**TCMT 16T304, Grade: HB7130-2****Order data**

Order number	260956 HB7130-2
GTIN	4062406750336
Item class	21G

Description

TCMT 16T304 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Grade	HB7130-2
Number of changes/inserts	3
Tool material	Carbide
Chip breaker	VS
Main application	M
Cutting depth a_p	0.2 - 1.5 mm
Cutting conditions	slightly interrupted
Corner radius	0.4 mm

ISO code indexable insert	TCMT 16T304
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 270 m/min
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning