

**Garant****VNMG 160408, Grade: HB7130-2**

## Order data

Order number	251734 HB7130-2
GTIN	4062406765033
Item class	21G

## Description

VNMG 160408 HB7130-2 Grade: HB7130-2

Chip breaker: VS

Cutting depth  $a_p$ : 0.3 - 2 mmFeed  $f$ : 0.05 - 0.4 mm/rev.Cutting speed  $v_c$  main application: 80 - 270 m/min

## Technical description

Number of changes/inserts	4
ISO code indexable insert	VNMG 160408
Chip breaker	VS
Cutting depth $a_p$	0.3 - 2 mm
Corner radius	0.8 mm
Tool material	Carbide
Cutting speed $v_c$ main application	80 - 270 m/min

Cutting conditions	slightly interrupted
Grade	HB7130-2
Main application	M
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.4 mm/rev.
Type of product	Indexable insert for turning