



Torque analyser for torque wrenches "SmartCheck USB", maximum torque: 1500N·m



Order data

Order number	654651 1500
GTIN	4018754331352
Item class	60N

Description

Version:

Variable and flexible torque wrench analyser with rotating display and base body. Can be mounted horizontally and vertically. The display and the membrane keypad are splash-proof and the body is made of impact-resistant plastic. **Micro-USB interface** for **data export** and for power supply. With memory capacity for 250 measured values.

3 user modes: Tracking display (**Track**), **trigger point sensing (First-Peak)**, **peak value display (Peak-Hold)**.

Units of measure: Nm, lbfft, lbf·in.

- **Robust.** The integrated visual and acoustic overload protection mechanism ensures a long working life.
- **Precise.** A display deviation of just $\pm 1\%$ guarantees extremely reliable measurement data.
- **Ready to start.** Thanks to the integrated transducer with large measurement range, you can get going straight away.
- **Flexible.** SmartCheck can be positioned almost anywhere. Whether installed horizontally or vertically – the well thought-out attachment points, compact design and rotatable display allow for all options.
- **Individual Three operating modes (Track, First Peak, Peak Hold) and three units of measurement (N·m, ft·lb, in·lb) are available. The target torque and tolerances for evaluating the measured value can be specified individually.**

- **Independent. For use at workstations without their own socket. In addition to conventional operation using a power supply unit, battery-powered operation is also possible.**
- **Rotatable. SmartCheck can be optimally adjusted in line with the specific viewing angle required. This is because not only the display, but also the display holder and base body can be rotated 180°.**
- **Stores up to 250 data records. Date and timestamp included.**
- **Data export and optional power supply via micro-USB port.**
- **Documentation software is free to download.**

Advantage:

Compact and variable torque analyser. Operation on power supply or batteries.

Application:

Adjusting and checking **torque screwdrivers and torque wrenches** with or without setting scale.

Supplied with:

Including power supply unit and SmartCheck USB software for transmitting values and creating test certificates. In a sturdy plastic case.

Note:

Suitable Bluetooth module available via eShop (No. 52110222).

Technical description

maximum torque	1500 Nm
Display unit width	120 mm
Torque measuring accuracy	±1 %
Display unit depth	167 mm
Weight	5.69 kg
Display unit height	124 mm
Power supply	Mains-powered
Measuring range	150 - 1500 Nm
Square socket	1 in
Manufacturer's designation	SMARTCHECK 1500 USB
Direction of tightening	For right and left-hand tightening
Interface	USB interface
Test certificate	Manufacturer's test certificate
Calibration	O4

Type of product

Torque testing device