



Face driver with Morse taper, Morse taper (MK): 4



Order data

Order number	327401 4
GTIN	4062406764593
Item class	32P

Description

Version:

- **Tip angle 60°, clamping Ø 17 mm – 54 mm.**
- **Clockwise and anti-clockwise rotation.**
- **Outstandingly suitable for use on lathes and when hobbing.**

Application:

For mounting in the headstock taper of the lathe.

Suitable for:

Lathe centres No. 321405, No. 321720, No. 321730 and 321740.

Supplied with:

Face driver with centring points 327410 and driver 327412.

Optional extras:

No. 327410 centring point, No. 327412 driver, No. 327414 damping elements.

Note:

Suitable taper sleeves for adapting in lathe chucks available on request.

Working range Ø: 28 - 50 mm

Clamping Ø D1: 26 mm

Reach B: 70.3 mm

Workpiece weight: 55 kg

External Ø: 52 mm

largest centre point Ø 60° A: 9 mm

Technical description

largest centre point Ø 60° A	9 mm
------------------------------	------

External Ø	52 mm
Working range Ø	28 - 50 mm
Workpiece weight	55 kg
Reach B	70.3 mm
Clamping Ø D1	26 mm
Push-off screw	no
Type of product	Face driver