

Garant
Solid carbide milling cutter MTC, uncoated, Ø h6 DC: 10mm

Order data

Order number	202247 10
GTIN	4045197571052
Item class	11X

Description
Version:

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

Technical description

Shank form	HA
No. of teeth Z	3
Feed f_z for slot milling in short-chipping aluminium	0.04 mm
Cutting edge $\varnothing D_c$	10 mm
Feed f_z for side milling in short-chipping aluminium	0.05 mm
Recess $\varnothing D_1$	9.2 mm
Corner chamfer width at 45°	0.2 mm
Overhang length L_1 incl. recess	58 mm
Shank $\varnothing D_s$	10 mm
Overall length L	100 mm
Flute length L_c	16 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6

Tolerance nominal \varnothing	h6
Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	MTC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	130 m/min	N
Aluminium (short chipping)	suitable	100 m/min	N
Alu > 10% Si	suitable	85 m/min	N
PMMA acrylic	suitable	140 m/min	N
PE-HD	Suitable	100 m/min	N
PA 66	Suitable	110 m/min	N
PEEK	suitable	100 m/min	N
PF 31	Suitable	85 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	100 m/min	N

Cu	Suitable	80 m/min	N
CuZn	Suitable	100 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

Services

Shank grinding Type HB

129100 HB