



Face driver with Morse taper, Morse taper (MK): 4



Order data

Order number	327403 4
GTIN	4062406765835
Item class	32P

Description

Version:

- Tip angle 60°, clamping \varnothing 17 mm – 54 mm.
- Clockwise and anti-clockwise rotation.
- Outstandingly suitable for use on lathes and when hobbing.

Application:

For mounting in the headstock taper of the lathe.

Suitable for:

Lathe centres No. 321405, No. 321720, No. 321730 and 321740.

Supplied with:

Face driver with centring points 327410 and driver 327412.

Optional extras:

No. 327410 centring point, No. 327412 driver, No. 327414 damping elements.

Note:

Suitable taper sleeves for adapting in lathe chucks available on request.

Working range \varnothing : 55 - 100 mm

Clamping \varnothing D1: 54 mm

Reach B: 104.1 mm

Workpiece weight: 100 kg

External \varnothing : 82 mm

largest centre point \varnothing 60° A: 20 mm

Technical description

Workpiece weight	100 kg
------------------	--------

largest centre point \varnothing 60° A	20 mm
Clamping \varnothing D1	54 mm
External \varnothing	82 mm
Reach B	104.1 mm
Working range \varnothing	55 - 100 mm
Push-off screw	no
Type of product	Face driver