

Garant
SNMG 120408, Grade: HB725-1


Order data

Order number	251224 HB725-1
GTIN	4062406765620
Item class	21G

Description

SNMG 120408 HB725-1 Corner radius: 0.8 mm
 Grade: HB725-1
 Chip breaker: UM1
 Cutting depth a_p : 0.2 - 6 mm
 Feed f : 0.05 - 0.6 mm/rev.
 Cutting speed v_c main application: 50 - 250 m/min

Technical description

Corner radius	0.8 mm
Chip breaker	UM1
ISO code indexable insert	SNMG 120408
Grade	HB725-1
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	50 - 250 m/min
Main application	UNI

Feed f	0.05 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Cutting depth a_p	0.2 - 6 mm
Type of product	Indexable insert for turning