

Garant

GARANT Master Alu FEED solid carbide drill, plain shank DIN 6535 HA, uncoated, Ø DC h7: 4,0-Xmm



Order data

Order number	122590 4,0-X
GTIN	4062406750817
Item class	11E

Description

Version:

3-cutter tool, specially developed for use at **very high feed rates** in aluminium. Outstandingly suitable for machines with **high power consumption** and stable machining conditions.

- **Specially developed cutter geometry, designed for very high feed rates, reduced cutting pressure and controlled chip breaking.**
- **Precision flute profile for reliable evacuation of chips.**
- **Achieve outstanding feed rates and tool life thanks to the third cutting edge.**

The sector-leading technology of the drill point for the tool guarantees optimum self-centring behaviour and permits spot drilling on irregular surfaces. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.

For **HB**: use order **No. 122591**.

For **HE**: use order **No. 122590 + 129100HE**. Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by +/-10% (minimum 1 piece).

Delivery time: 10 weeks.

Minimum order quantity: 5 pieces.

Technical description

Feed f in aluminium short-chipping	0.53 mm/rev.
Shank Ø D _s	6 mm

Tolerance nominal \varnothing	h7
Standard	DIN 6537
\varnothing range	4 - 4.7 mm
Number of cutting edges Z	3
Flute length L_c	36 mm
Overall length L	74 mm
Series	Master Alu
Coating	uncoated
Tool material	solid carbide
Version	6xD
Type	W
Point angle	130 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	300 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	200 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

Services

Shank grinding Type HE

129100 HE