

Garant
TC.T 16T304, Grade: HB725-1


Order data

Order number	260986 HB725-1
GTIN	4062406765798
Item class	21G

Description

TC.T 16T304 HB725-1 Grade: HB725-1
 Chip breaker: UM1
 Tolerance: M
 Cutting depth a_p : 0.2 - 4 mm
 Feed f : 0.05 - 0.5 mm/rev.
 Cutting speed v_c main application: 50 - 250 m/min

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	3
Corner radius	0.4 mm
Feed f	0.05 - 0.5 mm/rev.
Chip breaker	UM1
Cutting depth a_p	0.2 - 4 mm
Tool material	Carbide

ISO code indexable insert	TCMT 16T304
Grade	HB725-1
Tolerance	M
Main application	UNI
Cutting speed v_c main application	50 - 250 m/min
Cutting conditions	slightly interrupted
Type of product	Indexable insert for turning