

Garant
Solid carbide milling cutter HPC, ZOx, Ø f8 DC: 3mm

Order data

Order number	202248 3
GTIN	4045197271501
Item class	11X

Description
Version:

Sturdy roughing end mill **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

Application:

For roughing milling with high demands on the component surface.

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 202004.

Technical description

Feed f_z for side milling in short-chipping aluminium	0.045 mm
Feed f_z for slot milling in short-chipping aluminium	0.035 mm
Overhang length L_1 incl. recess	12 mm
Corner chamfer width at 45°	0.1 mm
Cutting edge $\varnothing D_c$	3 mm
Recess $\varnothing D_1$	2.7 mm
No. of teeth Z	3
Shank form	HA
Shank $\varnothing D_s$	6 mm
Overall length L	57 mm
Flute length L_c	8 mm

Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Tolerance nominal \varnothing	f8
Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	ZOX
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	500 m/min	N
Aluminium (short chipping)	suitable	480 m/min	N
Alu > 10% Si	suitable	240 m/min	N
CuZn	suitable	240 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable only under restricted conditions
Air	suitable only under restricted conditions
Services	
Shank grinding Type HB	129100 HB