

**Garant**
**DC.T 070204, Grade: HB7130-2**


### Order data

Order number	260353 HB7130-2
GTIN	4062406769215
Item class	21G

### Description

DC.T 070204 HB7130-2 Grade: HB7130-2  
 Chip breaker: VS  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 1.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 270 m/min

### Technical description

Number of changes/inserts	2
ISO code indexable insert	DCMT 070204
Tool material	Carbide
Cutting speed $v_c$ main application	80 - 270 m/min
Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing

Main application	M
Tolerance	M
Chip breaker	VS
Feed f	0.1 - 0.3 mm/rev.
Grade	HB7130-2
Cutting depth $a_p$	0.2 - 1.5 mm
Type of product	Indexable insert for turning