

Garant**VBMT 160402, Grade: HB7130-2**

Order data

Order number	261150 HB7130-2
GTIN	4062406769239
Item class	21G

Description

VBMT 160402 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Number of changes/inserts	2
Corner radius	0.2 mm
Grade	HB7130-2
Chip breaker	VS
Cutting depth a_p	0.2 - 1.5 mm
Main application	M
Finishing/roughing assignment	Finishing

Cutting conditions	slightly interrupted
Tool material	Carbide
ISO code indexable insert	VBMT 160402
Cutting speed v_c main application	80 - 270 m/min
Feed f	0.1 - 0.3 mm/rev.
Type of product	Indexable insert for turning