

Garant
DC.T 11T308, Grade: HB7130-2


Order data

Order number	260361 HB7130-2
GTIN	4062406769222
Item class	21G

Description

DC.T 11T308 HB7130-2 Grade: HB7130-2
 Chip breaker: VS
 Tolerance: M
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 80 - 270 m/min

Technical description

Chip breaker	VS
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting conditions	slightly interrupted
ISO code indexable insert	DCMT 11T308
Feed f	0.1 - 0.3 mm/rev.

Cutting speed v_c main application	80 - 270 m/min
Grade	HB7130-2
Cutting depth a_p	0.2 - 1.5 mm
Tool material	Carbide
Main application	M
Corner radius	0.8 mm
Type of product	Indexable insert for turning