



Pipe cutter DP50 for HT pipes, Type: 1



Order data

Order number	818190 1
GTIN	4003773087809
Item class	86A

Description

Version:

Tool body of glass-fibre-reinforced plastic. Exchangeable blade of high-quality ball bearing steel, can be changed with no tools required. Optimum pipe guidance and easy cutting thanks to self-adjusting rollers with plain bearings. The spring-mounted cutting blade means there is no need for tedious adjustment whilst cutting.

Advantage:

One tool, two functions, three diameters. **Easily and neatly cut and chamfer common plastic wastewater pipes in a single step.** Smooth cut: No adjustment, no deburring and a reduced risk of clogging or damage to the seal.

Application:

Cuts HT pipes and many other plastic pipes with Ø 32, 40 or 50 mm and a wall thickness of up to 2.4 mm. Easy to position thanks to clear view of the cut-off point. Final cuts or fine cuts are possible from a section length of approx. 10 mm.

Spare part:

For replacement blade see No. 818191 size 1 and replacement quick-change pivot pin No. 818192 size 1.

for pipe outer Ø: 32 mm

for pipe outer Ø: 40 mm

for pipe outer Ø: 50 mm

Length: 202 mm

Weight: 294 g

Technical description

for pipe outer Ø	32 mm
for pipe outer Ø	40 mm
for pipe outer Ø	50 mm
Weight	294 g
Length	202 mm
suitable for pipe material	Copper
suitable for pipe material	VA
suitable for pipe material	Brass
suitable for pipe material	Aluminium
Type of product	Pipe cutters

Accessories

Spare blade Type 1	818191 1
Spare quick-change axle Type 1	818192 1