

KERN
Counting scales, type CIB, maximum weighing range: 30kg

Order data

Order number	479541 30
GTIN	4045761214835
Item class	47D

Description
Version:

- **Precision counting scales with automatic reference optimisation (refines the average piece weight value in stages).**
- **Target quantity and target weight programmable to give an acoustic signal.**
- **Cumulative quantity memory for totalling weighings of identical parts by total quantity and total weight.**
- **Selectable reference piece numbers or reference weight.**
- **Selectable mains and battery operation.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Display selectable between pieces and weight.**

Checkweighing display: Acoustic or visual feedback if weighing is outside a pre-determined limit value.

Supplied with:

Mains adapter 230 V / 50 Hz, battery and protective hood.

Technical description

Dimensions of weighing plate	315x215 mm
Power supply	Rechargeable battery-powered
Power supply	Mains-powered

maximum weighing range	30 kg
Height	120 mm
Linearity	±4 g
Width	350 mm
Scale divisions	2 g
Net weight	3.6 kg
Reproducibility	2 g
Depth	330 mm
Settling time	2 s
Nominal voltage	240 V
Minimum unit weight	10 g
Calibration	K2
Type of product	Counting balance

Services

DAkkS calibrationScales maximum weighing range 50	027710 50
CalibrationScales maximum weighing range 50 kg	027700 50