

**Garant**
**Toolholder with ratchet long, All-steel, Overall length: 300mm**

**Order data**

Order number	149001 300
GTIN	4062406754693
Item class	11K

**Description**
**Version:**

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove centred and at each end for engaging the retaining ball. **Holder with stainless steel sheath.** Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness.

**Application:**

Suitable for tapping holes where access is difficult.

**Note:**

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

**Technical description**

Overall length	300 mm
for hand taps DIN 352	M5 – M12
Capacity □	4.5 - 8 mm
Spare jaws No. 148712 size	110

Material	All-steel
Type of product	Pin vice