

Garant

**Workstation with electric height adjustment Load capacity max. 250 / 200 kg
dark Eluplan worktop, Type: 1250/S**

**Order data**

Order number	920301 1250/S
GTIN	4062406755379
Item class	9GG

Description**Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **with** side plates, suitable for installing in a row.

Colour:

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

Recommendation:

Light assembly work, sitting and standing.

Note:

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

Technical description

Depth	750 mm
Worktop thickness	50 mm
Weight	98 kg
Control panel with display and memory functions	yes
Plug type, input	F

Nominal voltage	250 V
maximum load capacity	250 kg
Worktop depth	750 mm
Worktop length	1250 mm
ComfortClose	no
Width	1250 mm
Height adjustment range (worktop surface) from – to	720 - 1200 mm
Lifting speed	38 mm/s
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Continuous load capacity	250 kg
Material of worktop	Eluplan, dark
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table