

Garant**ZCMX 10T304, Grade: HBZ030**

Order data

Order number	268433 HBZ030
GTIN	4062406770105
Item class	21E

Description

Version:

Harder substrate for longer tool life with thinner CVD coating. Especially for facing and longitudinal turning applications.

Technical description

Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	70 - 200 m/min
ISO code indexable insert	ZCMX 10T304
Tool material	Carbide
Feed rate f when drilling	0.03 - 0.12 mm
Corner radius	0.4 mm
Cutting depth a_p	0.4 - 2 mm
Main application	P

Grade	HBZ030
Feed rate f when turning	0.1 - 0.3 mm
Cutting conditions	continuous
suitable for tool dia. D_c	20 mm
Type of product	Indexable insert for turning