


Garant**WNMG 080412, Grade: HB7130-2**

Order data

Order number	252072 HB7130-2
GTIN	4062406765057
Item class	21G

Description

WNMG 080412 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Grade	HB7130-2
Finishing/roughing assignment	Finishing
Chip breaker	VM
Number of changes/inserts	6
Corner radius	1.2 mm
Feed f	0.1 - 0.5 mm/rev.
Cutting conditions	slightly interrupted

Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	70 - 240 m/min
Main application	M
Tolerance	M
ISO code indexable insert	WNMG 080412
Tool material	Carbide
Type of product	Indexable insert for turning