

Garant**ZCMX 130404, Grade: HBZ030**

Order data

Order number	268443 HBZ030
GTIN	4062406770150
Item class	21E

Description

Version:

Harder substrate for longer tool life with thinner CVD coating. Especially for facing and longitudinal turning applications.

Technical description

ISO code indexable insert	ZCMX 130404
Feed rate f when drilling	0.03 - 0.12 mm
Grade	HBZ030
Cutting conditions	continuous
Feed rate f when turning	0.1 - 0.3 mm
Cutting depth a_p	0.4 - 2 mm
Corner radius	0.4 mm
Cutting speed v_c main application	70 - 200 m/min
Main application	P

suitable for tool dia. D_c	25 mm
Type of product	Indexable insert for turning