

Garant
PCD slot drill with internal cooling straight cut, PCD, Ø h10 DC: 16mm

Order data

Order number	209800 16
GTIN	4062406765132
Item class	100

Description
Version:

High performance PCD slot drill for high metal removal rates.

Axial angle 0°.

Straight flutes for a neutral cut.

Technical description

Feed f_z for side milling in graphite	0.15 mm
Direction of infeed	horizontal, oblique and vertical
Flute length L_c	20 mm
Feed f_z for side milling in cast aluminium	0.11 mm
Corner chamfer width at 45°	0.1 mm
Feed f_z for slot milling in graphite	0.15 mm
Corner chamfer angle	45 degrees
Tolerance nominal \varnothing	h10
Overall length L	125 mm
Feed f_z for slot milling in cast aluminium	0.1 mm
No. of teeth Z	2
Shank $\varnothing D_s$	16 mm
Cutting edge $\varnothing D_c$	16 mm

Shank	DIN 6535 HA with h6
Recess $\varnothing D_1$	15 mm
Overhang length L_1 incl. recess	30 mm
Coating	PCD
Tool material	PCD
Standard	Manufacturer's standard
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.2 \times D$ for side milling
Through-coolant	yes
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	2400 m/min	N
Aluminium (short chipping)	suitable	2000 m/min	N
Alu > 10% Si	suitable	1500 m/min	N
PMMA acrylic	suitable	1000 m/min	N
PE-HD	suitable	900 m/min	N
PA 66	suitable	900 m/min	N
PEEK	suitable	800 m/min	N
PVDF GF20	suitable	1200 m/min	N
POM GF25	suitable	1200 m/min	N
PA 66 GF30	suitable	1000 m/min	N
PEEK GF30	suitable	1000 m/min	N
PTFE CF25	suitable	1000 m/min	N
PEEK CF30	suitable	800 m/min	N
Hybrids	suitable		

MMC	suitable	400 m/min	N
GRP	suitable	500 m/min	N
CRP	suitable	500 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB