



Face driver with Morse taper, Morse taper (MK): 5



Order data

Order number	327402 5
GTIN	4062406765828
Item class	32P

Description

Version:

- Tip angle 60°, clamping \varnothing 17 mm – 54 mm.
- Clockwise and anti-clockwise rotation.
- Outstandingly suitable for use on lathes and when hobbing.

Application:

For mounting in the headstock taper of the lathe.

Suitable for:

Lathe centres No. 321405, No. 321720, No. 321730 and 321740.

Supplied with:

Face driver with centring points 327410 and driver 327412.

Optional extras:

No. 327410 centring point, No. 327412 driver, No. 327414 damping elements.

Note:

Suitable taper sleeves for adapting in lathe chucks available on request.

Overall length: 218 mm

Working range \varnothing : 40 - 72 mm

Clamping \varnothing D1: 38 mm

Reach B: 89 mm

Workpiece weight: 65 kg

External \varnothing : 70 mm

Technical description

Overall length	218 mm
----------------	--------

largest centre point \varnothing 60° A	14 mm
Working range \varnothing	40 - 72 mm
External \varnothing	70 mm
Reach B	89 mm
Workpiece weight	65 kg
Clamping \varnothing D1	38 mm
Push-off screw	no
Type of product	Face driver