

**Garant****Carbide masonry drill, Drill Ø: 10mm****Order data**

Order number	786070 10
GTIN	4062406773458
Item class	71C

**Description****Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

**Application:**

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

**Technical description**

Drill Ø	10 mm
overall length	120 mm
Flute length	80 mm
Shank Ø	10 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill

