

Garant
GARANT Master Mute boring bar shank vibration damping, 15×D, System / shank Ø: QC/25

Order data

Order number	264898 QC/25
GTIN	4062406773618
Item class	29E

Description
Version:

Shank carbide reinforced.

Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$.

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 430 mm

Centre offset H base body: 2.5 mm

non-clamping range S: 145 mm

recommended clamping length: 100 mm

Assembly bolt set: 269026 1

Technical description

Assembly bolt set	269026 1
non-clamping range S	145 mm
System	QC
Centre offset H base body	2.5 mm
Plug connector for coolant connection	269208

recommended clamping length	100 mm
High-pressure connecting hose	269207
Overall length L	430 mm
Series	Master Mute
Boring depth up to	15×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks