

Garant
**PCD torus cutter with internal cooling straight cut, PCD, Ø e8 DC / R1:
6/0,5mm**

Order data

Order number	209804 6/0,5
GTIN	4062406765354
Item class	100

Description
Version:

High performance PCD slot drill for **high metal removal rates.**

Straight flutes for a neutral cut.

Tolerance for corner radius $R_1 = \pm 0.01$ mm.

Technical description

Feed f_z for copy milling in graphite	0.12 mm
Feed f_z for side milling in graphite	0.07 mm
Overall length L	57 mm
Corner radius R_1	0.5 mm
Feed f_z for copy milling in cast aluminium	0.07 mm
Flute length L_c	6 mm
Feed f_z for side milling in cast aluminium	0.04 mm
Overhang length L_1 incl. recess	21 mm
Shank $\varnothing D_s$	6 mm
Cutting edge $\varnothing D_c$	6 mm
No. of teeth Z	2
Recess $\varnothing D_1$	5.5 mm

Shank	DIN 6535 HA to h6
Coating	PCD
Tool material	PCD
Standard	Manufacturer's standard
Tolerance nominal \varnothing	e8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.2×D for side milling
Through-coolant	yes
Shank tolerance	h6
Colour ring	black
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Aluminium	suitable	2400 m/min	N
Aluminium (short chipping)	suitable	2000 m/min	N
Alu > 10% Si	suitable	1500 m/min	N
PMMA acrylic	suitable	1000 m/min	N
PE-HD	suitable	900 m/min	N
PA 66	suitable	900 m/min	N
PEEK	suitable	800 m/min	N
PVDF GF20	suitable	1200 m/min	N
POM GF25	suitable	1200 m/min	N
PA 66 GF30	suitable	1000 m/min	N
PEEK GF30	suitable	1000 m/min	N
PTFE CF25	suitable	1000 m/min	N
PEEK CF30	suitable	800 m/min	N

Hybrids	suitable		
MMC	suitable	400 m/min	N
GRP	suitable	500 m/min	N
CRP	suitable	500 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable		
Air	suitable		
Services			

Shank grinding Type HB	129100 HB
------------------------	-----------