



AkkuSafe box, Type: 2



Order data

| | |
|--------------|---------------|
| Order number | 981119 2 |
| GTIN | 4003866405824 |
| Item class | 96L |

Description

Version:

High-quality special aluminium container for **secure storage** and **transportation of lithium-ion batteries**. Suitable for transporting prototypes, new / intact (UN 38.3 tested) as well as damaged or defective / critically defective batteries (observe specification / approval. Request if necessary) in accordance with **ADR SV 376** and packaging regulations **P911**, as well as batteries for disposal and recycling.

Successfully passed the fire test as per P911: maximum outside temperature below 100°C, no flames or splinters escaping in the event of an accident.

Non-flammable padding and absorbent material, non-conductive and dust-free. Foamed lid seal. Stackable, with convenient locks. Maximum gross weight, hazardous substance approval: 65 kg.

Approval for critical defective Li-ion batteries **up to 814 Wh**. Inside use: 3 compartments. No spread of flames to the adjacent rechargeable batteries.

Standard:

UN 3480, UN 3481, UN 3090, UN 3091, SV 376, P903, P908, P909, P910, P911 ADR, GGV.

Technical description

| | |
|--------|---------|
| Weight | 11.5 kg |
| Width | 600 mm |
| Height | 250 mm |
| Depth | 600 mm |

| | |
|---|----------------|
| Volume | 67 l |
| wheeled | no |
| Usable height | 120 mm |
| Usable depth | 430 mm |
| Usable width of the compartment | 120 mm |
| Number of handles | 2 |
| max. gross mass, hazardous substance approval | 65 kg |
| integrated rollers | no |
| Type of product | Aluminium case |