



AkkuSafe box, Type: 3



Order data

Order number	981119 3
GTIN	4003866405831
Item class	96L

Description

Version:

High-quality special aluminium container for **secure storage** and **transportation of lithium-ion batteries**. Suitable for transporting prototypes, new / intact (UN 38.3 tested) as well as damaged or defective / critically defective batteries (observe specification / approval. Request if necessary) in accordance with **ADR SV 376** and packaging regulations **P911**, as well as batteries for disposal and recycling.

Successfully passed the fire test as per P911: maximum outside temperature below 100°C, no flames or splinters escaping in the event of an accident.

Non-flammable padding and absorbent material, non-conductive and dust-free. Foamed lid seal. Stackable, with convenient locks. Maximum gross weight, hazardous substance approval: 65 kg. **Approval** for critical defective Li-ion batteries **up to 1348 Wh**. Flexible interior use. Highly resistant to puncture, also suitable for power tool batteries.

Standard:

UN 3480, UN 3481, UN 3090, UN 3091, SV 376, P903, P908, P909, P910, P911 ADR, GGV.

Technical description

Weight	11.5 kg
wheeled	no
Depth	400 mm
Volume	42 l

Height	250 mm
Width	600 mm
Usable width of the compartment	390 mm
Usable depth	190 mm
Usable height	100 mm
max. gross mass, hazardous substance approval	65 kg
integrated rollers	no
Number of handles	3
Type of product	Aluminium case