

Garant
WNMG 080404, Grade: HB725-1


Order data

Order number	252068 HB725-1
GTIN	4062406765705
Item class	21G

Description

WN.G 080404 HB725-1 Grade: HB725-1

Chip breaker: UN1

Tolerance: M

Cutting depth a_p : 0.2 - 6 mm

Feed f : 0.05 - 0.6 mm/rev.

Cutting speed v_c main application: 50 - 250 m/min

Technical description

ISO code indexable insert	WNMG 080404
Tool material	Carbide
Main application	UNI
Cutting depth a_p	0.2 - 6 mm
Cutting speed v_c main application	50 - 250 m/min
Cutting conditions	slightly interrupted
Tolerance	M

Chip breaker	UN1
Number of changes/inserts	6
Grade	HB725-1
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Feed f	0.05 - 0.6 mm/rev.
Type of product	Indexable insert for turning