

Garant
WNMG 060408, Grade: HB725-1


Order data

Order number	252064 HB725-1
GTIN	4062406765699
Item class	21G

Description

WN.G 060408 HB725-1 Grade: HB725-1
 Chip breaker: UN1
 Tolerance: M
 Cutting depth a_p : 0.2 - 6 mm
 Feed f : 0.05 - 0.6 mm/rev.
 Cutting speed v_c main application: 50 - 250 m/min

Technical description

Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting depth a_p	0.2 - 6 mm
Cutting speed v_c main application	50 - 250 m/min
Number of changes/inserts	6
Cutting conditions	slightly interrupted

Grade	HB725-1
Tool material	Carbide
Main application	UNI
Feed f	0.05 - 0.6 mm/rev.
Chip breaker	UN1
ISO code indexable insert	WNMG 060408
Tolerance	M
Type of product	Indexable insert for turning