

**Garant****ESD workstation with electric height adjustment Max. load capacity 250 kg,  
ESD worktop, Type: 1250/S****Order data**

Order number	972017 1250/S
GTIN	4062406773595
Item class	9GG

**Description****Version:**

ESD workstation with electric height adjustment. Non-conductive base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick volume conductive ESD worktop. Control panel is not ESD conductive. Work bench with side plates, conductive, light grey similar to RAL 7035, can be installed in a row.

**Colour:**

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

**Recommendation:**

Light assembly work, sitting and standing.

**Note:**

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

**Technical description**

Worktop thickness	50 mm
Worktop depth	750 mm
Weight	98 kg

Height adjustment range (worktop surface) from – to	720 - 1200 mm
maximum load capacity	250 kg
Depth	750 mm
Lifting speed	38 mm/s
Worktop length	1250 mm
Width	1250 mm
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	50 mm
electrostatic characteristic	EGB/ESD
Type of product	Work table