

**Garant**
**SNMG 120412, Grade: HB725-1**


## Order data

Order number	251226 HB725-1
GTIN	4062406765637
Item class	21G

## Description

SNMG 120412 HB725-1 Corner radius: 1.2 mm  
 Grade: HB725-1  
 Chip breaker: UM1  
 Cutting depth  $a_p$ : 0.2 - 6 mm  
 Feed  $f$ : 0.05 - 0.6 mm/rev.  
 Cutting speed  $v_c$  main application: 50 - 250 m/min

## Technical description

Feed $f$	0.05 - 0.6 mm/rev.
Cutting depth $a_p$	0.2 - 6 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	1.2 mm
Cutting conditions	slightly interrupted
Number of changes/inserts	8

ISO code indexable insert	SNMG 120412
Cutting speed $v_c$ main application	50 - 250 m/min
Grade	HB725-1
Main application	UNI
Chip breaker	UM1
Type of product	Indexable insert for turning