

**Garant**
**VNMG 160408, Grade: HB725-1**


### Order data

Order number	251804 HB725-1
GTIN	4062406765675
Item class	21G

### Description

VN.G 160408 HB725-1 Grade: HB725-1  
 Chip breaker: UM1  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 6 mm  
 Feed  $f$ : 0.05 - 0.6 mm/rev.  
 Cutting speed  $v_c$  main application: 50 - 250 m/min

### Technical description

ISO code indexable insert	VNMG 160408
Cutting speed $v_c$ main application	50 - 250 m/min
Cutting conditions	slightly interrupted
Number of changes/inserts	4
Cutting depth $a_p$	0.2 - 6 mm
Grade	HB725-1

Main application	UNI
Finishing/roughing assignment	Finishing
Tool material	Carbide
Chip breaker	UM1
Feed f	0.05 - 0.6 mm/rev.
Tolerance	M
Type of product	Indexable insert for turning